

DETAILED ITEM DESCRIPTION / SPECIFICATIONS:				
Item No	Material No	Material/Service Description	Quantity	Qty Uom
10		Autosampler PM Kit	1.000	Each
20		CHASSIS ASSY-NETLINKBOX	1.000	Each
30		FID ASXL/Clarus GC PM Kit	1.000	Each
40		MODULE ASS-HSXL PRESS CONTROL	1.000	Each

50		FILTER WHEEL GLUED L-20-40P	1.000	Each
60		ELP UV Lamp Complete	2.000	Each
70		Tungsten Halogen Lamp Assembly	2.000	Each

Form for request- New category/Sub Category Creation
Request form from Buyer

Details of Proposer	
Name-	Mr. S B Sadvelkar
Organisation	HPCL Mumbai Refinery
Email Address	sbsadvelkar@hpcl.in
Phone number	022-25076191
Product Details	Spares of UV Spectrophotometer LAMBADA 35 Units & PERKIN ELMER Clarus GC.
	1) Autosampler PM Kit 2)CHASSIS ASSY-NETLINKBOX 3)FID ASXL/Clarus GC PM Kit 4)MODULE ASS-HSXL PRESS CONTROL 5)FILTER WHEEL GLUED L-20-40P 6)ELP UV Lamp Complete 7)Tungsten Halogen Lamp Assembly
Function/Application	Spares of UV Spectrophotometer LAMBADA 35 Units & PERKIN ELMER Clarus GC. 1) Autosampler PM Kit :-Autosampler Consumable Parts Consist of 5uL Autosampler Syringe with vial loactor .Required for Benzene GC.. 2)CHASSIS ASSY-NETLINKBOX - DotLink Used in communication between PC Software & GC. Can be used for for both GCs. 3)FID ASXL/Clarus GC PM Kit :- It is device used FID Detector consumable parts. Required for Benzene GC. 4)MODULE ASS-HSXL PRESS CONTROL :-It's used to control N2 Makeup flow / FID H2 /FID Air flow. Can be used for both GCs.Currently required for Methanizer N2 5)FILTER WHEEL GLUED L-20-40P :- Is the device Wavelength Filter. 6)ELP UV Lamp Complete :-UV Source Lamp 7)Tungsten Halogen Lamp Assembly :-Tungsten Source Lamp
Governing Standards	NA
	1) Autosampler PM Kit :- for Clarus GC, Model- Clarus 500 Part No. N9300308/90279090 2)CHASSIS ASSY-NETLINKBOX :- for Clarus GC, Model- Clarus 500 Part No N9300306/90279090 3)FID ASXL/Clarus GC PM Kit :- for Clarus GC, Model- Clarus 500 Part No N9300306/90279090 4)MODULE ASS-HSXL PRESS CONTROL :-for Clarus GC, Model- Clarus 500 Part No N6100309/90328990 5)FILTER WHEEL GLUED L-20-40P :- for UV Spectrophotometer, LAMBADA 35 Part No B2000122/90021900 6)ELP UV Lamp Complete :-for UV Spectrophotometer, LAMBADA 35 Part No L6022728/85394900 . 7)Tungsten Halogen Lamp Assembly : for UV Spectrophotometer, LAMBADA 35 Part No BO114620/85392990Spares
LOVs/Ratings	NA
Certifications/Approval	NA
License	NA
Test requirements	NA
Estimated Annual Drawl	NA
One time/Recurring	One Time
OEM Catalogues	NA
Expected price	NA
Variant/Range/Rating Of the Product	NA
Safety Standards Applicable or not	NA
If any Statutory/Legal Requirement applicable for this product	NA
Details of Legal Documentation	NA
Spare parts details of the requisite product if applicable	NA
OEMs/Sellers Details	
OEM-1/Seller-1	

Name	OEM M/s M/S PerkinElmer Scientific (Singapore)Pte Ltd. Indian Subsidiary- M/s M/S Spectralytic Scientific India Private Limited Thane Maharashtra
Email id	Email: India.CustomerCare@PERKINELMER.COM
Email id	Harshad.Sawant@PERKINELMER.COM
Address	C/o ProConnect Supply Chain Solutions Pvt. Ltd.,No. J Block R K Logiworld Near Khodiyar Dham, Yewai Village,Bhiwandi, Thane, Maharashtra, 421302
Contact Number	75062 50139
OEM-2/Seller-2	
Name	
Email id	
Address	
Contact Number	
OEM-3/Seller-3	
Name	
Email id	
Address	
Contact Number	
Previous order copies/Tenders	NA
Product Catalogues	NA
Priority of the requirement	Critical
Details of 3 prospective Buyers	
Buyer-1	
Name	HPCL
Email id	
Address	
Contact Number	
Buyer-2	
Name	IOCL
Email id	
Address	
Contact Number	
Buyer-3	
Name	BPCL
Email id	
Address	
Contact Number	
Previous order copies/Tenders	NA