

Specifications for Dehumidifier required in cold module

1.	Application	Seed Cold Storage
2.	Room Volume (L x B x H)	8" x 7" x 7" ft
3.	% Relative Humidity (RH) to be maintained	40% (Max)
4.	Average Cold Module Temperature	4°C \pm 2°C
5.	Number of Persons in cold module	Nil
6.	Number of doors and door size of cold module	1 Door (Door Size : 7" x 3")
7.	Average Door opening / day	<i>at least</i> 7- times
8.	Number of fixed opening and size	NO fixed opening

Prices should include its installation, its interlinking with air conditioners of the cold module, humidity meter installation.